see the latest versions of our order forms, please visit www.sorgrollstuhltechnik.de/download-porta



Quotation **Order**

Weight capacity: 90 kg

Base price 7.995,- €

Prices excl. VAT, valid from 15.01.2024 and until further notice.

Dynamic wheelchair system for people with uncontrolled movements. Suitable for children, teenagers and adults.

Configurable as a complete system with ergonomic seat and back unit or as a base for assembling a seat shell from a specialist retailer

- Frame grows with the child without purchasing parts, SW by 4 cm (in 2 cm steps)
- pneumatic or solid tyres
- Standard knee lever brake and drum brake
- Long back guide with adapter, e.g. for seat shells with a physiological pivot point.
- Closed frame for high stability
- Height-adjustable push handle

Delivery address / Company stamp:	Billing address: ☐ same as delivery address
Name:	Name:
Address:	Address:
Ordering information:	
Reference/ internal description:	Date:
Contact person:	Signature:

Thanks to its suspension systems, the innovative Dynamis TSD wheelchair system guides the forces and movements (e.g. bei during stretch spasms) into the cushioning elements of the wheelchair, instead of blocking them.



26-50 cm (+2/+4 cm)



seat depth **28-52 cm** (+2 cm)



back height 35-65 cm



wheel sizes 16", 20", 22" and 24"



wheel camber von -3° to +30°

spring-loaded headrest





weight capacity 90 kg

Further advantages of the Dynamis TSD

ADJUSTABLE BACK SUSPENSION by means of spring damping (patent pending). This can be quickly and easily adjusted to the required strength. A time consuming search for the correct strength of a gas pressure spring is no longer necessary. Supportive rebound return to the preset basic back angle setting (90°, 95° oder 100°).

Thanks to the **spring-loaded headrest**, the risk of tension/injuries in the neck/





pring-loaded

N° 138201

configuratin - cf.


Please select type of use



Base for the ERGO-Version \square Seat frame as the base for a SORG ERGO back and seating system already contains: - Height-adjustable push handles, dynamic legrest (standard), continuously adjustable back suspension by means of steel spring damper, Rebound-function, Ergonomic seat and back unit made of aluminum (without cushion), growing by + 2 / + 4 cm in width and +2 cm in depth. back guide for ERGO seat and back unit

or

935,-€






Configuration seat shell version

Items when used as a base for a seat shell from a specialist retailer

Universal seat plate for seat shell screw connection ☐ Universal seat plate for screwing a seat shell manufactured by a specialist retailer N° 192904 105,-€



N° 12	0,-€
Push handles	
Extendable by 20 cm, angle adjustable by 307 with metal joint	N N
Please choose a height setting:	
(Setting can be changed later, without selection = standard pushing height)	
\square (14) Standard pushing height 90 - 100 cm (+7 cm for RF	150)


(..15) Pushing height high 100 - 110 cm (+7 cm for RH 50)

N° 6531...

Back angle Factory setting (The setting can be changed later): N°698210 □ 95° N°698211 ☐ 100° N°698212 If not selected, 90° is the standard setting

If you use your own seat shell, please go

directly to page 5.







Configuration of the ERGO version

The following articles on this page and on page 4 are reserved exclusively for the ergonomic seat and back unit

ERGO-back	cushion		
WITHOUT ERGO back cushion	Anatomically shaped back cushion for ERGOback (in the middle about 3 cm thick), with lateral support and slight lumbar support. incl. cover choice of cover color see below	ADDITIONAL cover for ERGO back cushion in chosen cover color	WITHOUT cover for ERGO-back cushion
	N° 891300 CPD 740,- €	N° 891301 230,-€	N°998912 ./. 120,- €

ERGO-seat	ERGO-seat cushion							
WITHOUT ERGO seat cushion	anatomically formed seat cushion for ERGO-seat incl. cover choice of cover color see below	☐ Incontinence cover for seat cushion	ADDITIONAL cover for seat cushion in chosen cover color	■ WITHOUT cover for seat cushion				
	N° 891002 CPD 499,- €	N° 891004 190,-€	N° 891003 186,-€	N°998001 ./. 30,-€				

Side uphols	tery							
☐ Side upholstery inside for ERGO seat cushion								
WITHOUT	(cushion thickness per side approx. 2,5cm)							
side uphols-								
tery	incl. cover, choice of cover color see below							
	Choosing side upholstery reduces the selected seat width by 5 cm							
	N° 458205	CPD 169,- €						

Choice	of Trevira	a cover color	lote: Color views may di	ffer from reality depending	on the screen view / pr	rintout and are only for in	nitial orientation.		
Please	choose you	r color of the ch	osen covers (back	/ seat / ERGO-side	guards):				
☐ bla	ack (30)	☐ grey (31)	☐ night blue (32)	ultramarine blue	33) petrol (34)	☐ applegreen (35)) ☐ burgundy (36)	☐ red (37)	□ pink (38)
N° 80	(seat cush	nion/anat. cushi	on) / I	N°85 (back cushic	n/anat. back cus	hion) / N°	4582 (side uphol	stery)	

Back configuration (choose back height A	AND assembl	y height of p	ush bar)					Back angle
Back height ERGO-version (N°12 5)	□ 35	□ 40	□ 45	□ 50	□ 55	□ 60	□ 65	Factory basic setting. (The setting can be changed later):
Push handle overall height adjustment of 20 cm possible, 307° adjustable	at BH 35 /	neight push 40 / 45: dard sliding heig			height pus 55 / 60 / 6 ndard sliding hi	☐ 90° N°698210 ☐ 95° N°698211 ☐ 100° N°698212		
in angle by steel joint PLEASE SELECT THE ASSEMBLY HEIGHT				□(13) High sliding hide 107-117 cm without selection, the standard installation height				Without selection is 90 °
N° 6531 0,- €	height applies			applies				the default

Pivot point seat-/back unit

configuratin - cf.

So that we can pre-assemble the optimal pivot point of the seat and back unit, please choose between the upper and lower pivot point.


Pre-assembly on:

□ lower pivot point (For people **UP TO** 150 cm bodyheight) (..20)

(For people **STARTING AT** 150 cm bodyheight) □ upper pivot point (..21)

Without selection = upper pivot point for pre-assembly

N° 6982.



Lateral support Lateral support holder FOLDABLE Lateral support holder FIX Pad (incl. removable cover) for holder Size 1: for holder Size 2: ☐ Foldable lateral support holder ☐ Screwed lateral support holder, incl. linkage, extension and protective cover incl. linkage □ 10 x 7 cm (..0104)□ 12 x 9 cm (..0206) Without Pads Without Pads □ 10 x 9 cm (..0105)☐ 15 x 10 cm (..0204) Length difference of the holder Size 1 to Length difference of the holder Size 1 to size 2 is about 4.5cm □ 12 x 9 cm (..0106)□ 18 x 13 cm (..0205) size 2 is about 4.5cm Adjustable in height Linkage for holder Size 1: Linkage for holder Size 2: 12 x 9 cm / 15 x 10 cm / 18 x 13 cm 10x7cm / 10x9 cm / 12x9 cm N°6859.. CPD 116,- € / P N° 6859.. CPD 116,- € / P Protective 10x7cm 10x9cm 12x9cm 15x10cm 18x13cm N°68590213 CPD 544,- € / P N°68591082 CPD 118,- € / P

Sun shade			
only up to SW38) variably adjustable sun shade, in black Usable height (from the top edge of the seat plate to the apex) = selected back height + 45 cm Example: BH 40 + 45 cm = 85 cm	size 2 (just from SW40) variably adjustable sun shade, in black Usable height (from the top edge of the seat plate to the apex) = selected back height + 55 cm Example: BH 40 + 55 cm = 95 cm	☐ Extension set Increasing the usable amount of the Sun shade by 14 cm.	
N° 910301 TD 250,- €	N° 910302 TD 290,- €	N° 910305 TD 58,- € / Set	

End of the ERGO-configuration, continue on page 5

for general configuration.



configuratin - cf.

From here: General configuration

The following articles are suitable for use with the ERGO seat and back unit and the seat shell base.

Seat width / seat depth configuration:


Selection of seat width AND seat depth Info on tilting: A gas pressure spring is installed up to seat width 36; From seat width 38, two gas pressure springs are always installed. measurements in cm seat width (N° 10..) seat depth (N° 11..) 28 30 32 50 Frame size 26 34 36 38 40 42 44 46 48 28


Ci-o O	00							
Size 0	32							
(N°1300)	34							
	36							
Ci-o 1	32							
Size 1	34							
(N°1301)	36							
Ci-o O	38							
Size 2 (N°1302)	40							
(N 1302)	42							
Ci-a 2	44							
Size 3 (N°1303)	46							
	48							
Size 4	50							
(N°1304)	52							

ERGO-version

(View from above)

The seat depth is without upholstery






Seat shellversion (View from above)

Dynamic leg support

for Standard-LLL

□ Dynamic leg support for standard lower leg length



Possible distance top edge seat to top edge footplate: 31 to 45 cm

for short LLL

□ Dynamic leg support for short lower leg length



Possible distance top edge seat to top edge footplate: 23,5 to 33 cm

Leg support options

Equinus foot suspension



N° 405405 128,-€

Locking mechanism

Locking mechanism at 90° for dynamic leg supports 405400/01

Heel cups inclusive straps

alu black, inclusive straps for heel cups (with velcro fastener)

- \square size 1 (...21) (up to foot width 6,5 cm)
- ☐ size 2 (...22) (til foot width 8,5 cm) (from SW 28 cm)


size 3 (..23) (til foot width 9,5 cm) (from SW 30 cm)



Width adjustable footplate

☐ Undivided foot plate, depth 230 mm, adjustable in width by max. 80 mm (depending on model and configuration). Offers the option of setting the maximum usable width individually

- Only in combination with N ° 405400 - Not in combination with heel edge max, 40mm



0,- € N° 405401 Calf pads for dynamic leg supports

☐ Two-part calf pad,

N° 403007

padding thickness 2 cm, adjustable in height and width Including elastic Nylon cover. black.



Foot fixation

295,- € N° 4009


247,- € N° 7812.

with Velcro fastener and pulley inclusive belt buckles for self-assembly

- □ sz. 1 (..01)
- □ sz. 2 (..02)

□ sz. 4 (..03)

64,- € N° 4020..



Circum-Size ference C 15-20 cm 2 19-23 cm 24-28 cm

199,-€/P

SORG Rollstuhltechnik GmbH + Co. KG, Benzstraße 3-5, D 68794 Oberhausen-Rheinhausen / Germany, fon +49 7254-9279-0, fax +49 7254-9279-10, info@sorgrollstuhltechnik.de, www.sorgrollstuhltechnik.de As of: 13. Mai 2024, 8:45 Uhr. Illustrations may differ from actual product execution. Technical alterations and misprints excluded.

Maximum adjustable Wheelchair dimension = seat height - 8 cm; Final dimension distance max. 45 cm

Specify: Lower leg length (LLL) Specify: **Cushion thickness** Result: Wheelchair dimensions Distance upper edge of the seat and the upper edge of the footplate - Cushion thickness



All measurements in cm

Lower leg length:

Specification of the distance in cm between the hollow of the knee and the sole of the foot at a 90 $^\circ$ knee position angle

Thickness seat cushion:

Indication of the thickness of the planned seat cushion

Wheelchair Dimensions:

Distance from the upper edge of the seat to the upper edge of the footrest in cm (without taking into account the thickness of the seat cushion). From your information regarding the lower leg length and thickness of the seat cushion, we calculate the distance from the top edge of the seat to the top edge of the footrest and mount this on the leg support you have chosen.

Example:

Your information: LLL = 31 cm, seat cushion thickness = 5 cm **Manufacturer assembly:** In this example, SORG mounts the footrest at a distance of 26 cm from the footrest.

Selection of seat height / rear wheels size												
	Seat height (in cm), without seat cushion											
rear wheel	41											
16"				月//								
20"	月//											
22"												
24"			²	²								
possible caster wheels sizes	5"	5"-5,5"	5"-6"	5"-7"	5"-7"	5"-7"	5"-7"	5,5"-7"				

If the seat depth is smaller than the specified seat depth, there may be a conflict with the tilting (armrest <-> wheel cover) 1 = from seat depth 34 2 = from seat depth 38

]	
	= Possible without restrictions.
	= Not possible.
	= Recommended, but not with frame size 4 or SD 28-34
	= 1 Possible but due to the conflict het

Lower leg length

armrests and wheel protection, the entire tiltable space may not be available AND


2. not with frame size 4 or SD 28-34

Caster wheels				
Standard PU	Standard solid rubber	Standard pneumatic	Design PU	Design solid rubber
Polyurethan: □ 5" (2805) □ 6" (2803)	Solid rubber: 5" (2809) 5,5" (2802) 6" (2811) 7" (2813)	Pneumatic, grey: G 6" (2808) 7" (2807)	Polyurethane, transparent, with LEDs: □ 5" (2834)	Solid rubber, black, with alu rim 5" (2836) 6" (2838)

Caster forks		Caster wheel options		
Standard Aluminum Design Aluminum		Track fixation	Locking	
Alu fork, black anodized	Aluminum fork coated in frame color color N°: The color numbers can be found next to the frame colors on page 8. Without specifying a color number, the selected frame color is used for coating. Anodized colors are only possible	Caster wheel track fixation (straight)	☐ Locking mechanism for track fixation	
	in the design package.			
N° 2826 0,- €	N° 2829 TD 70,- € / P	N° 2851 166,- € / P	N° 2850 208,- € / P	

configuratin - cf.

Rear wheels 20"- 24" Wheel size as on page 6 configured (when selecting seat height / rear wheel size)						
Rear wheel Standard Rear wheel with Profile handrim Only with 22" and 24						
☐ All-round wheel, silver, with drum brake hub	Standard wheel, silver, with closed, rubb Unity of rim and handrim, reduces the risk of injury to the fingers. Additional weight compared to lightweight wheels: approx. 1400g per pair. Additional weight compared to standard wheels: approx. 900g per pair.	erized, black profile handrim.				
N° 2130 0,- €	N° 2132	96,- €/P				





The color numbers can be found

Anodized colors only possible in the design package

for coating.

490,- €/P N°303000

next to the frame colors on page 8

Without specifying a color number, the selected frame color is used

N°33. 368,- €/P N°341501... 460,- €/P N°34.. Handrim options Silicone cover for standard handrim Detachable silicone cover, black (soft surface) for Standard wheel □ 20" (20)□ 22" (22)□ 24" (24)156,- / P

function.

with profile


handrims

Spoke cover		Spoke cover design decors only for wheelsize 20"-24"			
Transparent		Please specify the desired model of the corresponding manufacturer:			
☐ transparent (00) Only for wheelsize 20"-24"		□ www.speichen-schutz.de	_	□ www.wheelchairgadgets.com	_
N° 25	172,- € / P	N° 2526	TD 180,- € / P	N° 2527	TD 180,-€/P

Wheel cover			
for rear wheels 16"-	24"		
Wheel cover long for 20", 22" and 24"		Wheel cover short for 16", 20", 22" and	
N° 5210	220,- € / P	N° 5211	180,- € / P

Colors					
Frame colors (frame / ergonomic seat and back unit)					
Finish alternatives	Moderate metallic effect	Not metallic	Special colors (without addition	onal charge, except for Nightblue)	
matt (not possible with special colors)	□ Cream white (17) □ Brilliant Blue (08) □ Zinc yellow (02) □ Dark Blue (16) □ Chrome yellow (06) □ Dark Green (15) □ Pure Orange (21) □ Goblin Green (33) □ Crimson (04) □ Titan Grey (34) □ Girly Pink (19) □ King´s Blue (32) □ Pastel Blue (20)	☐ Black (31)	strong metallic-effect: ☐ Silver metallic (36) Coarse structured surface: ☐ Coarse black (27)	Dormant colors: ☐ Firered (45) ☐ Violet (50) Dormant color with add. charge: ☐ Nightblue (47) AC 90,- €	
Design package color	anodization (Color examples for anodized colo	rs can be found on our we	ebsite in the area equipment)		
□ anodized blue (01) □ anodized red(02) □ anodized green (03) □ anodized green (03) □ anodized goldorange (04) □ anodized goldorange (05) □ anodized violet (05) ■ no (1573 CPD 295,- € The following parts are anodized (if installed): caster wheel assembly (caster forks, adapters, half shells, track widening), profile tube supports of the push handle, gas pressure spring holder, handrims. The design package ist only possible in the listed setting. Restrictions: The handrims are only available in the design package a colors by choosing aluminum handrims. (not possible with stainless steel, Maxgrepp, PVC, double or nob handrims. not possible with wheels with profile handrims)			andrims. (not possible with double or nob handrims. Also		


Raw delivery				
Raw state	Subsequent coating			
☐ of the following components:	☐ in chosen frame color.			
3-part ERGO-back,	Components:			
ERGO-seat, ERGO-side guards	3-part ERGO-back,			
	ERGO-seat, ERGO-side guards			
N° 999950 0,-	€ N° 999915 220,- €			




configuratin - cf.



Positioning aids







Positioning belts		
Article name	Article-N°	Price
☐ 2-Point pelvic belt with PLASTIC fastener, incl. mounting material for self attachment	N° 780590	140,-€
☐ 2-Point pelvic belt with METAL fastener, incl. mounting material for self attachment	N° 780591	155,-€
☐ 4-Point pelvic belt with PLASTIC fastener, incl. mounting material for self attachment	N° 780592	180,-€
☐ 4-Point pelvic belt with METAL fastener, incl. mounting material for self attachment	N° 780593	195,- €
□ Protection cap for pelvic belt with metal fastener (see N° 780591 oder N° 780593) Makes independent opening for the patient difficult.	N° 78050210	19,- €
☐ Chest-shoulder belt without zipper, incl. mounting material for self attachment	N° 781010	199,-€
2-point pelvic belt plastic fastener 2-point pelvic belt metal fastener 2-point pelvic belt plastic fastener 2-point pelvic belt metal fastener 4-point pelvic belt metal fastener Application ex	5 Chest-shoulded belt	6

Upper belt holder	Lower belt holder			Belt buckles	"extra-strong"	
upper belt holder For fastening the belt buckles of the selected belt (here: chest-shoulder belt).	lower belt holder, both sides The belt buckles of the selected belt are attached to the holders.			Extra strong belt buckles for pelvic belts / chest-shoulder belt Suitable up to a maximum belt width of 25 mm. These additional belt buckles will be included in the delivery.		
				Pieces	Article-N°	Price
				☐ 2 pieces	N° 78011102	TD 35,- €
Supplied loose or mounted on the he-	4 attachment points		-	☐ 4 pieces	N° 78011104	TD 68,- €
adrest (if ordered)	for belt buckles (2x left, 2x right)	O /		☐ 6 pieces	N° 78011106	TD 100,- €
N° 780130 95,- €	N° 780100		64,- €	☐ 8 pieces	N° 78011108	TD 133,- €

Frame options/equipment					
Anti-tipper	Wheel base extension	Rigid frame	Outdoor front end	Splash guard	
swing-away Mounting: pair	N° 7676 274,- Step tube mounting left right pair	or increased Torsional stiffness Frame does not grow with the width. Not possible with seat width 26 and 28	Outdoor Front End, adjustable in width and length, facilitates significantly active and passive driving on soft or rough surfaces, incl. mounting aid.	Splash guard for Outdoor Front End, made of plastic	
N° 721599 0,	- € N° 7400 74,-	N° 597695 419,-€	N° 599520 CPD 479,- €	N° 59951212 CPD 85,- €	

Transport brackets				
Compatibility with electrical drive systems or Outdoor-Front-End	Transport brackets			
Please tick appropriate box if number N° 58507610 was selected (Without tipping an appropriate box, delivery will be without compatibility to additional systems): Outdoor-Front-End (restraint brackets at the front) Neither Restraint brackets must be replaced by a subsequent fitting of an Outdoor-Front-End or an electrical drive system to the wheelchair	☐ Transport brackets (4 pieces) for transportation in a handicapped accessible passenger car	CRASH TESTED ISO 7176-19		
	N°58507610	CPD 386,- €		

Notes:

Terms and conditions

configuratin - cf.

(1) Our terms and conditions apply exclusively. Any deviating, opposing, or complementing terms and conditions on the part of the business partner do not form integral part of contract unless explicitly ap-proved of by us. There are no exceptions to the consent requirement, which also applies in cases where we conduct deliveries without restrictions while aware of the business partner's terms and conditions. (2) Agreements made in the individual case with the purchaser (including side-agreements, supplements, and alterations) always take priority over these terms and conditions. A contract or our confirmation - both in written form - are authoritative for the content of such arrangements.

(3) Any legally relevant declarations and notifications the purchaser submits to us after conclusion of the contract (e.g. setting of deadlines, notice of defects, declarations of rescission or abatement) require the written form to be valid.

(4) Any information on the application of legal regulations serves the mere purpose of clarification. All regulations are legally binding without any such clarifications unless explicitly altered or excluded in these terms and conditions.

All prices are ex works, excluding insurance and packaging. The prices are net prices; the value-added tax is stated and charged separately according to the legally binding rate at the time of invoicing. The prices valid on the day of delivery are binding unless explicitly arranged otherwise.

3. Conclusion of Contract

SORG's offers are invitatio ad offerendum (invitations to treat). Ordering goods counts as an obligatory offer of contract on the part of the purchaser. Unless the order suggests otherwise, we have the right to accept this contract offer within two weeks time after reception. The acceptance of an offer of contract is effected by the confirmation of the order.

(1) Provided that no other agreements exist, payment is to be made by paying in advance - 50% at placing of order, 50% pre-delivery of goods. The purchaser bears any costs arising from transactions

(2) If a 30-day payment deadline is exceeded, a delay rate of 9% on top of the respective base rate of table 1 a 30-day payment deather its executed, a death yate of 30 map of its perfect respective by the European Central Bank falls due without the need for prior notices. Beyond that, the purchaser is charged 3,-€ for any reminder sent. We reserve the right to make use of the commercial due rate according to § 353 HGB. A higher damage for delay may be enforced via a suitable verification.

Offers and Validity

All current price lists are generally valid until December 31 of the respective year, or until new price lists are published. The latest version of the price list will always be provided on our homepage. Offers older than 3 months at that point expire and must be replaced with new offers and prices.

We state the terms of delivery when accepting the order. The delivery date is non-binding and has mere guideline value - especially with regard to customised products. The terms for delay in delivery are defined by legal regulations. In any case, a writing notice issued by the purchaser is necessary for them to take effect.

(1) SORG is not to be held responsible for the following delays of delivery. This also applies if these causes occur with respect to legal representatives, auxiliary persons, or deliverers of SORG: Circumstances of force majeure as well as other extraordinary events that are unpredictable and unavoidable for, and not caused by, SORG, and that only occur after ordering or reserving, and that SORG could not have known about. Moreover, this applies in case of strikes, fire, floods, labour disputes, business disruptions, altered magisterial approbation and legal situation, and magisterial orders which are not due to operational risks

(2) In the cases of paragraph 1, SORG is eligible to delay delivery/performance for the time of hin-drance as well as an appropriate start-up time. If SORG thus causes unacceptable complications for the purchaser, both SORG and the purchaser are eligible to withdraw from the contract. Circumstances that only lead to a temporal and hence acceptable delay of delivery and performance are excluded from this right. The legal rights of the client remain unaffected.

We generally dispatch uncovered by insurance and at the recipient's risk. We transfer the risk of coincidental loss or deterioration of the goods as well as delay on to the client at the moment of passing the goods on to the forwarder, bearer, or any other person/institute responsible for delivery. SORG will make any effort to respect the client's wishes in terms of path and kind of delivery. Any costs caused by

this (including agreed carriage free delivery) are to be covered by the client. In the case of carriage free delivery conducted by SORG, the recipient is required to put forward any carriage costs for a refund. If the client wishes the dispatch to be delayed, any risk of loss or deterioration of the goods is carried by the recipient from the first day of readiness for dispatch. The goods dispatched are only insured upon special demand and at the cost of the recipient.

9. Damage through DeliveryAngelieferte Gegenstände sind, auch wenn sie unwesentliche M\u00e4ngel Upon delivery, the goods need to be checked for obvious damage in the presence of the bearer. Any damage is to be documented in a written form and co-signed by the bearer. This protocol is to be forwarded to us immediately. Delayed reclamations, or reclamations not signed by the bearer, cannot be taken into

10. Warranted Features, Receipt, and Technical Alterations
Delivered objects, even with minor damage, are to be accepted by the client, even if §433.paragraph 1 BGB is not fulfilled. Partial deliveries are permissible. Features only count as warranted if explicitly designated as such. A warranty of condition can only be asserted explicitly and in a written form. SORG reserves the right for technical alterations, especially for solutions of equal or higher value.

(1) SORG warrants for any defects of delivered new goods for 12 months as long as the purchaser is not the user (§§ 474, 13 BGB). Should the purchaser be the user then the warranty period is two years for new goods, for used goods 12 months. Should the purchaser also be an entrepreneur, then the

liability for used items is void, as long as there is no claim for compensation according to N°12.

(2) The purchaser's claim for defects presuppose that he has attended his obligation to give notice of defects on the legal grounds for his reasons of inquiry (§§ 377, 381 HGB). If defects are found during the inspection or at a later point, we are to be notified in writing without delay. The notice counts as not delayed if issued within two weeks. Posting the notice on time suffices for the keeping of the term. Independently from this obligation to inspect and give notice, the purchaser is to report obvious defects (including wrong and short delivery) within two weeks upon delivery (again, posting the notice on time suffices). If the purchaser misses the proper inspection and/or notice of defects, we do not warrant for the reported defects. If the delivered good is defected, we may choose to conduct supplementary performance either by repairing the defect (subsequent improvement) or by delivering flawless goods (compensation delivery). Our right to refuse the chosen method of supplementary performance on the respective legal grounds remains untouched.

(3) Our liability for defects expires when alteration or maintenance works are done by the client or a

third-person-party without our prior written permission. Consequences of excessive strain, negligent or incorrect handling, and violent damage are excluded from the warranty for defects.

12. Further Liability

(1) With respect to compensation - regardless of the legal cause - SORG is only liable in case of malice and act of gross negligence. In case of slight negligence, SORG is only liable for damage of life, body, health, and for damage caused by the negligence of an essential contractual obligation (an obligation whose fulfilment make the proper realisation of the contract possible in the first place and in whose fulfilment the contract partner regularly trusts and can trust). In this case, however, our liability does not exceed the covering of predictable, typically occurring damage.

(2) A free right to termination on the part of the purchaser (acc. to § 651, 649 BGB in particular) is

precluded. Otherwise, the usual prerequisites and legal consequences apply.

13. Costs of Supplementary Performance

Costs of supplementary performance cannot be charged on SORG's account.

14. Voluntary Withdrawal of Goods

SORG is not obliged to take back any delivered end products or parts thereof. If SORG voluntarily decides otherwise in individual cases (especially for therapeutically altered requirements or deaths), SORG refunds a maximum of 75% of the delivery costs for unused parts whose delivery does not date back more than three months. There is no legal obligation concerning withdrawal in this respect. Deliveries which date back more than three months as well as sewed parts and customised products are not returnable. A copy of the delivery note or the bill serves as proof of age of delivery.

Goods delivered by SORG remain the property of SORG until any obligations from the parties' business contract on the part of the purchaser have been redeemed. This also applies if SORG has adapted individual or all claims into a running account which has been balanced and acknowledged. The purchaser has the right to dispose of the goods in the proper course of business. The purchaser hereby yields all claims to SORG which arise from the resale against the purchaser or third parties. The purchaser is authorised to withdraw these claims even upon conveyance. SORG's right to withdraw the claims remains untouched. However, SORG is obliged not to withdraw the claims as long as the purchaser complies with his duty of payment and any other duties. SORG has the right to demand that the purchaser makes known the yielded claims and their debtors, that he provides all information necessary for conveyance, and that he hands in all associated documents. As long and insofar the reservation of ownership is intact, the purchaser must not transfer any goods for securing or bailment without SORG's permission. The purchaser must not transier any goods for securing or bailment without SORG's permission. The purchaser may process or alter the goods for the benefit of SORG exclusively. If processed with other goods which do not belong to SORG, SORG obtains co-ownership of these new goods in relation to the invoice value to the cost price of the other processed goods. If a third party interferes with SORG's ownership, the purchaser is to notify SORG immediately. The purchaser must not make any agreements with other purchasers which may exclude or limit SORG's rights. In particular, the purchaser must not make any agreements which destroy or limit the advance assignments to SORG. If the estimated value of the existing guarantees exceeds the claims to be ensured by more than 20%, SORG is insofar obliged to release by request of the purchaser.

16. Copyright Protection

In Copyright rolection of weight or measurements, technical documentations, or other product descriptions and documents (including electronic ones), the respective indications only apply if explicitly stated that they do. SORG reserves ownership and copyright of all these documents. They may only be made available to third parties upon SORG's explicit permission. explicit permission

17. Place of Fulfilment, Place of Jurisdiction, and Severability Clause (1) The law of the Federal Republic of Germany applies for these Terms and Conditions and all legal

relations between us and our business partners. All international and supranational (contractual) legal systems, the UN Convention on Contracts for the International Sale of Goods in particular, are hereby excluded. Prerequisites and effects of the reservation of ownership acc. to no. 15 are subject to the right of the respective storage location of the good if the choice of law made in favour of the German law is illegitimate or ineffective. The only place of jurisdiction (also on an international basis) for any disputes arising directly or indirectly from the contractual relationship is, according to German Commercial Code, our office in Oberhausen-Rheinhausen, Germany. However, we also have the right to file a suit concerning the general jurisdiction of the purchaser.

(2) If any clause in these Terms of Conditions should turn out to be ineffective, this does not affect the ectiveness of all other clauses

Technical alterations and misprints reserved. As of: January 2017 SORG Rollstuhltechnik GmbH + Co. KG Benzstr. 3-5, 68794 Oberhausen-Rheinhausen / Germany Phone +49 7254 / 9279-0 Fax +49 7254 / 9279-10 info@sorgrollstuhltechnik.de, www.sorgrollstuhltechnik.de